


# Specifications



## Eaton TR5362CDV

Eaton Arrow Hart heavy duty industrial specification grade duplex receptacle, Tamper resistant, auto-grounding, Dual control, #14-10 AWG, 20A, Flush, 125V, Ivory, Brass, Impact-resistant thermoplastic face, PVC body, 5-20R, 2-pole, 3-wire, ,

### General specifications

<b>PRODUCT NAME</b>	Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle
<b>CATALOG NUMBER</b>	TR5362CDV
<b>UPC</b>	032664744655
<b>PRODUCT LENGTH/DEPTH</b>	1.3 in
<b>PRODUCT HEIGHT</b>	4.19 in
<b>PRODUCT WIDTH</b>	0.84 in
<b>PRODUCT WEIGHT</b>	0.22 lb
<b>CERTIFICATIONS</b>	cULus Listed



*Powering Business Worldwide*

## Product specifications

<b>DEVICE TYPE</b>	Receptacle
<b>TYPE</b>	Dual control
<b>AMPERAGE RATING</b>	20A
<b>VOLTAGE RATING</b>	125V
<b>CONTACT MATERIAL</b>	Brass
<b>FEATURES</b>	Tamper resistant Auto-grounding Dual-controlled
<b>APPLICATION</b>	Industrial
<b>DEVICE GRADE</b>	Construction
<b>WIRING METHOD</b>	Back and side
<b>NUMBER OF WIRES</b>	Three-wire
<b>MOUNTING METHOD</b>	Flush
<b>NUMBER OF POLES</b>	Two-pole
<b>STYLE TYPE</b>	Standard
<b>COLOR</b>	Ivory
<b>CONNECTION TYPE</b>	Screw
<b>ALLOWABLE WIRE SIZE</b>	#14-10 AWG
<b>NEMA CONFIGURATION</b>	5-20R
<b>TORQUE RATING</b>	14 lbf-inch
<b>DESIGN TYPE</b>	Straight blade
<b>FACE/BODY MATERIAL</b>	PVC Body Impact-resistant thermoplastic face
<b>RECEPTACLE TYPE</b>	Duplex

## Resources

<b>BROCHURES</b>	<a href="#">Spec grade receptacles brochure</a> <a href="#">Controlled receptacles sell sheet</a>
<b>MULTIMEDIA</b>	<a href="#">Residential straight blade receptacles</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - TR5362CDV</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.


Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications



## Eaton TR5362CDV

Eaton Arrow Hart heavy duty industrial specification grade duplex receptacle, Tamper resistant, auto-grounding, Dual control, #14-10 AWG, 20A, Flush, 125V, Ivory, Brass, Impact-resistant thermoplastic face, PVC body, 5-20R, 2-pole, 3-wire, ,

### General specifications

<b>PRODUCT NAME</b>	Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle
<b>CATALOG NUMBER</b>	TR5362CDV
<b>UPC</b>	032664744655
<b>PRODUCT LENGTH/DEPTH</b>	1.3 in
<b>PRODUCT HEIGHT</b>	4.19 in
<b>PRODUCT WIDTH</b>	0.84 in
<b>PRODUCT WEIGHT</b>	0.22 lb
<b>CERTIFICATIONS</b>	cULus Listed



Powering Business Worldwide

## Product specifications

<b>DEVICE TYPE</b>	Receptacle
<b>TYPE</b>	Dual control
<b>AMPERAGE RATING</b>	20A
<b>VOLTAGE RATING</b>	125V
<b>CONTACT MATERIAL</b>	Brass
<b>FEATURES</b>	Tamper resistant Auto-grounding Dual-controlled
<b>APPLICATION</b>	Industrial
<b>DEVICE GRADE</b>	Construction
<b>WIRING METHOD</b>	Back and side
<b>NUMBER OF WIRES</b>	Three-wire
<b>MOUNTING METHOD</b>	Flush
<b>NUMBER OF POLES</b>	Two-pole
<b>STYLE TYPE</b>	Standard
<b>COLOR</b>	Ivory
<b>CONNECTION TYPE</b>	Screw
<b>ALLOWABLE WIRE SIZE</b>	#14-10 AWG
<b>NEMA CONFIGURATION</b>	5-20R
<b>TORQUE RATING</b>	14 lbf-inch
<b>DESIGN TYPE</b>	Straight blade
<b>FACE/BODY MATERIAL</b>	PVC Body Impact-resistant thermoplastic face
<b>RECEPTACLE TYPE</b>	Duplex

## Resources

<b>BROCHURES</b>	<a href="#">Spec grade receptacles brochure</a> <a href="#">Controlled receptacles sell sheet</a>
<b>MULTIMEDIA</b>	<a href="#">Residential straight blade receptacles</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - TR5362CDV</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

