



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

TY27M 13.38" Ty-Rap (Bulk)

Abb Installation Products, Inc

Catalog Number	TY27M
Manufacturer	Abb Installation Products, Inc
Description	High Performance Cable Tie, Black Color Nylon 6.6, Length Of 340MM (13.4 Inches) For Bundle Diameter Up to 102MM (4 Inches), Width Of 6.86MM (0.27 Inch), Tensile Strength Rating Of 534 Newtons (120 Pounds), Operating Temperature Of -30 Degrees Celsius (-22 F) to 85 Degrees Celsius (185 F), Bulk Pack
Weight per unit	0.0110 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	120;534
------------------	---------

Dimensions and Weight

Length	13.5
Thickness	0.06
Width	0.27

Descriptions

Description	13.38" TY-RAP (BULK)
extra long description	ABB TY27M CABLE TIE 120LB 13.4IN NA
Long Description	High Performance Cable Tie, Black Color Nylon 6.6, Length of 340mm (13.4 Inches) for Bundle Diameter up to 102mm (4 Inches), Width of 6.86mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -30 Degrees Celsius (-22 F) to 85 Degrees Celsius (185 F), Bulk Pack
Product Type	Cable Tie 120LB 13.4IN Natural Nylo
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210824697
Manufacturers Part Number	TY27M
UPC	786210824697

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 500

Packaging

Carton 500

Package 1000

Weight Per each 0.011

Uses, Certifications, and Standards

standard UL E49405