

Specifications



Photo is representative

Eaton V48M28T4516CU

Eaton General purpose ventilated transformer, DOE 2016, NEMA 2, FR940, 60 Hz, 220°C, 45 kVA, Three-phase, 480 Delta V, 208Y/120 Vac, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 150°C, 45 kVA, 480 Vac-208Y/120 Vac,

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	V48M28T4516CU
UPC	786680192005
PRODUCT LENGTH/DEPTH	21.13 in
PRODUCT HEIGHT	36.88 in
PRODUCT WIDTH	24.88 in
PRODUCT WEIGHT	362 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	10 CFR Part 431 (2016) Efficient



Physical Attributes

COIL MATERIAL	Copper
---------------	--------

Performance Ratings

EFFICIENCY	10 CFR Part 431-2016 (DOE)
------------	----------------------------

ENCLOSURE	NEMA 2
FRAME	FR940
INSULATION	220 °C
MATERIAL	Copper windings
MOUNTING	Floor or wall, upright only
TAP SIZE	2 at +2.5%, 4 at -2.5%
TYPE	Energy-efficient ventilated type DT-3 transformer

	2016)
FREQUENCY RATING	60 Hz
KVA RATING	45 kVA
PRIMARY VOLTAGE	480 V
SECONDARY VOLTAGE	208Y/120 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	150 °C rise
VOLT AMPERE RATING	45 kVA
VOLTAGE RATING	480 Vac-208Y/120 Vac

Resources

BROCHURES

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - V48M28T4516CU](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton V48M28T4516CU

Eaton General purpose ventilated transformer, DOE 2016, NEMA 2, FR940, 60 Hz, 220°C, 45 kVA, Three-phase, 480 Delta V, 208Y/120 Vac, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 150°C, 45 kVA, 480 Vac-208Y/120 Vac,

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	V48M28T4516CU
UPC	786680192005
PRODUCT LENGTH/DEPTH	21.13 in
PRODUCT HEIGHT	36.88 in
PRODUCT WIDTH	24.88 in
PRODUCT WEIGHT	362 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	10 CFR Part 431 (2016) Efficient



Physical Attributes

COIL MATERIAL	Copper
---------------	--------

Performance Ratings

EFFICIENCY	10 CFR Part 431-2016 (DOE
------------	---------------------------

ENCLOSURE	NEMA 2
FRAME	FR940
INSULATION	220 °C
MATERIAL	Copper windings
MOUNTING	Floor or wall, upright only
TAP SIZE	2 at +2.5%, 4 at -2.5%
TYPE	Energy-efficient ventilated type DT-3 transformer

	2016)
FREQUENCY RATING	60 Hz
KVA RATING	45 kVA
PRIMARY VOLTAGE	480 V
SECONDARY VOLTAGE	208Y/120 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	150 °C rise
VOLT AMPERE RATING	45 kVA
VOLTAGE RATING	480 Vac-208Y/120 Vac

Resources

BROCHURES

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - V48M28T4516CU](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

