

Specification Grade Ground Fault Circuit Interrupter Receptacles


2-Pole, 3-Wire Grounding
 15A, 125V/AC
 20A, 125V/AC
 NEMA 5-15, 5-20




5-15R




5-20R



VGFI5-AG



VGFS15-MSP



VGFD20

Specification Grade Automatic Ground GFCIs

Back Wire & Side Wire

15A, 125V
 NEMA 5-15R

20A, 125V
 NEMA 5-20R

Description	Catalog No. Color Suffix	Catalog No. Color Suffix
Auto Ground Duplex GFCI	<input type="checkbox"/> VGF15__-AG V, W	<input type="checkbox"/> VGF20__-AG V, W
Tamper Resistant Duplex GFCI	<input type="checkbox"/> TRVGF15__-AG BK, V, W	<input type="checkbox"/> TRVGF20__-AG BK, V, W

Includes standard size unbreakable wallplate

Specification Grade Combination GFCI Receptacle & Switch

Back Wire & Side Wire

15A, 125V
 NEMA 5-15R

Description	Catalog No. Color Suffix
NEMA 5-15 GFCI Receptacle with Feed-Through Single-Pole Switch (rated 1800W @ 120V/AC, 60Hz)	<input type="checkbox"/> VGFS15__-MSP V, W

Includes mid-size unbreakable wallplate

Specification Grade Blank Face GFCI

Back Wire & Side Wire

20A, 125V

Description	Catalog No. Color Suffix
Blank Face (Dead Front) GFCI, Rated as 1.5HP Motor Control Switch	<input type="checkbox"/> VGFD20__ V, W

Includes standard size unbreakable wallplate

Color Ordering Information

For ordering devices, include Cat. No. followed by the color code: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), RN (Orange), V (Ivory), W (White)

Icon Key

NAFTA Compliant - see page O-30

Tamper Resistant

Accessories for GFCIs

Description	Catalog No.
GFCI 7/8" extension ring Add color suffix: B (Brown), BLK (Black), LA (Light Almond), V (Ivory), W (White)	<input type="checkbox"/> GFER__
Metal self-closing horizontal 1-gang weather protective cover, decorator opening	<input type="checkbox"/> S1966
While-In-Use metal weather protective standard depth 1-gang cover, vertical mount	<input type="checkbox"/> WIUMV-1

Specification Information:

Specification Grade GFCI: G-13

Specification Grade Combo GFCI Receptacle & Switch: G-14

Specification Grade Blank Face GFCI: G-14



GFER



S1966



WIUMV-1

Specification Grade Ground Fault Circuit Interrupters

2-Pole, 3-Wire Grounding
Combo: 15A, 125V/AC Receptacle; 15A, 120V/AC Switch
Dead Front: 20A, 125V/AC

	Device Type	Specification Grade Combination GFCI Receptacle & Switch, 15A: VGFS15, ___-MSP	Specification Grade Blank Face (Dead-Front) GFCI, 20A: VGFD20 Series
	Wiring Type	Back & side wire	Back & side wire
	Testing & Code Compliance	<ul style="list-style-type: none"> cULus Listed to UL 498 and UL 943, file no. E60120 	<ul style="list-style-type: none"> cULus Listed to UL 498 and UL 943, file no. E60120
		<ul style="list-style-type: none"> Meets all UL 943 (GFCI), UL 498 (Receptacles), UL 20 (Switch) and applicable CSA requirements 	<ul style="list-style-type: none"> Meets all UL 943 (GFCI), UL 498 (Receptacles), UL 508 (Motor Control) and applicable CSA requirements
		<ul style="list-style-type: none"> NOM certified 	<ul style="list-style-type: none"> NOM certified
Specifications: Environmental	Flammability	Meets UL 94 requirements; V2 rated	Meets UL 94 requirements; V2 rated
	Temperature Rating	-35°C to 66°C (-40°F to 150.8°F)	-35°C to 66°C (-40°F to 150.8°F)
Specifications: Electrical	Dielectric Voltage	Withstands 2000V per UL 498	Withstands 2000V per UL 498
	Current Interrupting	Yes, at full-rated current	Yes, at full-rated current
	Temperature Rise	Max. 30°C (86°F) after 100 cycles of overload @ 150% of rated current (DC)	N/A
	Short Circuit Testing	Meets and exceeds 10 kA	Meets and exceeds 10 kA
Specifications: Mechanical	Terminal Accommodation	#14 - #10 AWG	#14 - #10 AWG
	Voltage Ratings	Permanently marked on device	Permanently marked on device
	Horsepower Ratings	Switch rated for motor loads per UL 20: 15A: @ 120V/AC = 1/2 HP, max. amps: 12 full-load amps	Rated for motor loads per UL 508: 20A: @ 125V/AC = 1.5 HP, max. amps 20 full load amps
Materials:	Top Housing	Thermoplastic, nylon	Thermoplastic, nylon
	Bottom Housing	PVC	PVC
	Strap	0.047" thick steel, zinc plated	0.047" thick steel, zinc plated
	Line Contacts	0.030" thick brass	N/A
	Terminal & Ground Screws	#8-32 steel, brass plated; neutral screw nickel plated, ground screw green	#8-32 steel, brass plated; neutral screw nickel plated, ground screw green
	Terminal Clamps	0.070" thick steel	0.070" thick steel