



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## UAG112 1-1/2" Ua Sealtite Conduit, Bonded UI 50'

*Southwire Company*

Catalog Number	UAG112
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 1-1/2 In Trade Size, 1.865 to 1.90 In Conduit Outer Diameter, 1.575 to 1.6 In Conduit Inner Diameter, TITAN2(TM) UI Style, 50 FT Length, Jacket: Thermoplastic;Core: Steel, Hot Dip Galvanized, Gray, 9 In Bend Radius, -67 °F Operating Temperature, +176 °F Operating Temperature, 113 LB/100 FT
Weight per unit	1.1 (lbs/each)
Product Category	Liquid Tight Conduit

### Features

outside diameter	1882
------------------	------

### Descriptions

Description	1-1/2" UA SEALTITE CONDUIT, BONDED UL 50'
extra long description	SWC 55093205 Titan2 Type UL Liquidt

### Manufacturer Information

GTIN	00032886042355
UPC	032886042355

### Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	LTM-UL

### Packaging

Carton	50
Weight Per each	1.13