



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WP3479GY Nickel 1 GHZ F Insert Gy

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | WP3479GY |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Achieve Reliable Connections With The Non-Recessed Nickel F-Connector In Gray. This Connector Supports Home Audio, Home Theater Audio, and Video Distribution, Ensuring Clear Signal Transmission and Durable Performance. This Insert Is Designed For Use In All Keystone Wall Plates and Features A Standard Rca Front Jack and F-Coaxial Rear For High-Quality Audio and Video Distribution. |
| Weight per unit | 0.0022 (lbs/each) |
| Product Category | Outlets, Jacks, & Plates |

Material, Color, and Finish

| | |
|-------|------|
| Color | Gray |
|-------|------|

Descriptions

| | |
|------------------------|---|
| Description | NICKEL 1 GHZ F INSERT GY |
| extra long description | OnQ WP3479GY NICKEL 1 GHZ F INSERT, |
| Long Description | Achieve reliable connections with the Non-Recessed Nickel F-Connector in gray. This connector supports home audio, home theater audio, and video distribution, ensuring clear signal transmission and durable performance. This insert is designed for use in all Keystone Wall Plates and features a standard RCA front jack and F-coaxial rear for high-quality audio and video distribution. |
| Product Type | Nickel 1 GHZ F Insert, Gy |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | Pass & Seymour/Legrand |
| GTIN | 00804428008330 |
| Manufacturers Part Number | WP3479GY |
| UPC | 804428008330 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | Residential GFCI devices |
|----------------------|--------------------------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 60 |
| Weight Per each | 0.0022 |