



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



XJG24 3/4" Conduit Expansion Fitting W/Integral Ground

Crouse-Hinds

Catalog Number	XJG24
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series XJG Expansion Coupling, Rigid/Imc, Steel, 4" Maximum Conduit Movement, 3/4" Trade Size
Weight per unit	2.0 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

dimensions	8.3000 IN X 5.1000 IN X 3.4000 IN
Material	ELECTROGALVANIZED STEEL

Descriptions

Description	3/4" CONDUIT EXPANSION FITTING W/INTEGRAL GROUND
extra long description	CRS-H XJG24 3/4 CND EXP JNT INT GRD
Features	"XJG conduit expansion couplings for EMT and rigid/IMC are used with EMT, rigid metal conduit and IMC to couple together two sections of conduit subject to longitudinal movement. They are installed indoors or outdoors in long conduit runs to permit linear movement caused by thermal expansion and contraction to prevent damage to conduit supports and electrical systems in building or bridges. XJGs for rigid/IMC and EMT are also available with a hot dip galvanized finish (standard for trade sizes 1-1/4" and
Long Description	Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Steel, 4" maximum conduit movement, 3/4" trade size
Product Type	3/4 CND Exp JNT Int GRD Max CND MVT 4

Manufacturer Information

Brand	Eaton
GTIN	00782274915746
Manufacturers Part Number	XJG24
UPC	782274915746

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Expansion coupling

Packaging

Carton	1
Weight Per each	1.95



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

Enclosure
standard

NEMA FB1
UL 514B, CSA C22.2