



IP65 Rotary Handle Mechanism <sup>①②③④</sup>




|   | Description   | Enclosure Rating     | Pkg. Qty. <sup>⑤</sup> | Catalog Number      |
|---|---|----------------------|------------------------|---------------------|
| <b>XTPAXRHM_</b><br>   | <b>Complete Kits—Includes Handle, Shaft and Required Hardware</b>         |                      |                        |                     |
|   | Rotary handle mechanism—black <sup>⑥</sup>                                | IP65                 | 1                      | <b>XTPAXRHMB</b>    |
|   | Rotary handle mechanism—red/yellow <sup>⑦</sup>                           | NEMA 12<br>UL/CSA 4X | 1                      | <b>XTPAXRHMR</b>    |
|   | Rotary handle mechanism—black—rotated 90° from vertical <sup>⑧</sup>      |                      | 1                      | <b>XTPAXRHM90B</b>  |
|   | Rotary handle mechanism—red/yellow—rotated 90° from vertical <sup>⑦</sup> |                      | 1                      | <b>XTPAXRHM90RY</b> |
| <b>XTPAXRHMSFT</b><br> | <b>Separate Parts</b>   |                      |                        |                     |
|   | Shaft only—includes shaft to mount to XTPR, 175 mm length                 | —                    | 10                     | <b>XTPAXRHMSFT</b>  |

**XTPAXSW**

## Sealing Facility

| Description   | Pkg. Qty. <sup>⑤</sup> | Catalog Number |
|---|------------------------|----------------|
| To prevent tampering with the overload release and the test function. It can be sealed using industry standard sealing wire. For use with XTPR manual motor protectors. | 5                      | <b>XTPAXSW</b> |

Three-Phase Commoning Links <sup>⑧</sup>



| For Use with...   | Qty. MMP | MMP Frame Size | Pkg. Qty. <sup>⑤</sup> | Catalog Number     |
|---|----------|----------------|------------------------|--------------------|
|   | 2        | B              | 10                     | <b>XTPAXCLKA2</b>  |
|   |          | D              | 1                      | <b>XTPAXCLKA2D</b> |
|   | 3        | B              | 10                     | <b>XTPAXCLKA3</b>  |
|   |          | D              | 1                      | <b>XTPAXCLKA3D</b> |
|   | 4        | B              | 10                     | <b>XTPAXCLKA4</b>  |
|  | 2        | B              | 10                     | <b>XTPAXCLKB2</b>  |
|   |          | D              | 1                      | <b>XTPAXCLKB2D</b> |
|   | 3        | B              | 10                     | <b>XTPAXCLKB3</b>  |
|   |          | D              | 1                      | <b>XTPAXCLKB3D</b> |
|   | 4        | B              | 10                     | <b>XTPAXCLKB4</b>  |
| 5   | B        | 10             | <b>XTPAXCLKB5</b>      |                    |
|   | D        | 1              | <b>XTPAXCLKB5D</b>     |                    |
|  | 2        | B              | 10                     | <b>XTPAXCLKC2</b>  |
|   | 4        | D              | 1                      | <b>XTPAXCLKC4D</b> |

For parallel power feed to several manual motor protectors on terminals 1, 3 and 5.

**Notes**

- ① Plug-in connection shafts, XTPAXRHMSFT\_ can be cut to desired length for mounting depths of 100–240 mm. Carrier with extension shaft included.
- ② With ON/OFF switch position and “+” (tripped), lockable with 3 padlocks, 4–8 mm hasp. Can be locked in the OFF position, if required.
- ③ Rotary handle mechanisms ship with door interlock disabled. See instruction publication with product for how to enable door interlock.
- ④ Not for use with XTPAXFAEM20 early-make front-mount auxiliary contact.
- ⑤ Orders must be placed in multiples of package quantity listed.
- ⑥ For use on main switches to IEC/EN 60204.
- ⑦ For use on main switches with emergency-stop function to IEC/EN 60204.
- ⑧ Protected against accidental contact. Frame B short-circuit proof  $U_0 = 690V$ ,  $I_0 = 63A$ . Frame B links can be combined by rotating mounting.

## IP65 Rotary Handle Mechanism ①②③④













|   | Description   | Enclosure Rating     | Pkg. Qty. ⑤ | Catalog Number      |
|---|---|----------------------|-------------|---------------------|
| <b>XTPAXRHM_</b><br>   | <b>Complete Kits—Includes Handle, Shaft and Required Hardware</b> |                      |             |                     |
|   | Rotary handle mechanism—black ⑥                                   | IP65                 | 1           | <b>XTPAXRHMB</b>    |
|   | Rotary handle mechanism—red/yellow ⑦                              | NEMA 12<br>UL/CSA 4X | 1           | <b>XTPAXRHMRY</b>   |
|   | Rotary handle mechanism—black—rotated 90° from vertical ⑥         |                      | 1           | <b>XTPAXRHM90B</b>  |
|   | Rotary handle mechanism—red/yellow—rotated 90° from vertical ⑦    |                      | 1           | <b>XTPAXRHM90RY</b> |
| <b>XTPAXRHMSFT</b><br> | <b>Separate Parts</b>   |                      |             |                     |
|   | Shaft only—includes shaft to mount to XTPR, 175 mm length         | —                    | 10          | <b>XTPAXRHMSFT</b>  |

**XTPAXSW**

## Sealing Facility

| Description   | Pkg. Qty. ⑤ | Catalog Number |
|---|-------------|----------------|
| To prevent tampering with the overload release and the test function. It can be sealed using industry standard sealing wire. For use with XTPR manual motor protectors. | 5           | <b>XTPAXSW</b> |

## Three-Phase Commoning Links ⑧

| For Use with...  | Qty. MMP  | MMP Frame Size | Pkg. Qty. ⑤        | Catalog Number     |
|--|---|----------------|--------------------|--------------------|
| <br><br><br><br><br> | 2   | B              | 10                 | <b>XTPAXCLKA2</b>  |
|  |   | D              | 1                  | <b>XTPAXCLKA2D</b> |
|  | 3   | B              | 10                 | <b>XTPAXCLKA3</b>  |
|  |   | D              | 1                  | <b>XTPAXCLKA3D</b> |
|  | 4   | B              | 10                 | <b>XTPAXCLKA4</b>  |
|  |   | D              | 1                  | <b>XTPAXCLKA4D</b> |
| 5  | B   | 10             | <b>XTPAXCLKA5</b>  |                    |
|  | Each MMP with one auxiliary contact or trip-indicating auxiliary contact fitted on the right  |                |                    |                    |
| <br><br><br><br>  | 2   | B              | 10                 | <b>XTPAXCLKB2</b>  |
|  |   | D              | 1                  | <b>XTPAXCLKB2D</b> |
|  | 3   | B              | 10                 | <b>XTPAXCLKB3</b>  |
|  |   | D              | 1                  | <b>XTPAXCLKB3D</b> |
|  | 4   | B              | 10                 | <b>XTPAXCLKB4</b>  |
| D  |   | 1              | <b>XTPAXCLKB4D</b> |                    |
| 5  | B   | 10             | <b>XTPAXCLKB5</b>  |                    |
|  | Each MMP with an auxiliary contact and trip-indicating auxiliary contact mounted on the right or a voltage release mounted on the left. |                |                    |                    |
|   | 2   | B              | 10                 | <b>XTPAXCLKC2</b>  |
|  |   | 4              | D                  | 1                  |

For parallel power feed to several manual motor protectors on terminals 1, 3 and 5.

**Notes**

- ① Plug-in connection shafts, XTPAXRHMSFT\_ can be cut to desired length for mounting depths of 100–240 mm. Carrier with extension shaft included.
- ② With ON/OFF switch position and “+” (tripped), lockable with 3 padlocks, 4–8 mm hasp. Can be locked in the OFF position, if required.
- ③ Rotary handle mechanisms ship with door interlock disabled. See instruction publication with product for how to enable door interlock.
- ④ Not for use with XTPAXFAEM20 early-make front-mount auxiliary contact.
- ⑤ Orders must be placed in multiples of package quantity listed.
- ⑥ For use on main switches to IEC/EN 60204.
- ⑦ For use on main switches with emergency-stop function to IEC/EN 60204.
- ⑧ Protected against accidental contact. Frame B short-circuit proof  $U_0 = 690V$ ,  $I_0 = 63A$ . Frame B links can be combined by rotating mounting.